

## EDITORIAL GUIDELINES FOR SUBMITTING A PAPER TO EXPERIMENTAL TECHNIQUES

Experimental Techniques (E/T) is a bi-monthly news magazine designed for the practicing engineer or technician. E/T is devoted to relatively brief and informal "how-to-do-it" (or how-not-to-do-it!) articles, emphasizing experimental, analytical and computational techniques and methods.

### LENGTH

The length of your article should not exceed six 8.5 x 11 inch double-spaced typewritten pages, including all text, tables, references, etc., but excluding illustrations (limit to four illustrations). If your paper is accepted for publication, you will be asked to provide the text of that article on a disk, noting the software and format of the disk.

### ILLUSTRATIONS

Each illustration should be prepared on a separate sheet, properly identified by the figure number and author's name. Graphs, charts and line drawings should be drawn in black ink on heavy white paper. Either the original drawings or high-quality, reproducible prints are required. Photographs must be black and white glossy prints. Letters, numbers or captions on illustrations must be in proportion to the illustration so that they are legible if the figure is reduced or enlarged when printed.

### FIGURE CAPTIONS

A separate list of figure captions is required.

Your manuscript will be reviewed by the E/T Editorial described above. After acceptance, E/T reserves the right to edit the paper

for grammar and usage. Any paper accepted by E/T becomes the property of the Society for Experimental Mechanics, Inc. to be published in E/T and other SEM publishing vehicles.

Please send an original and two copies of the manuscript, list of figure captions, and illustrations to:

*Dr. Henry R. Busby/ET  
The Ohio State University  
206 West 18th Avenue  
Dept. of Mechanical  
Engineering  
Columbus, OH 43210*

Please indicate your complete mailing address, telephone, fax and e-mail in a cover letter. In the case of multiple authors, indicate which author is to receive future correspondence regarding the submittal. ■

## ONE SYSTEM FOR ALL COHERENT OPTICAL NDT !

It fits in a PC and gives you the most advanced real-time interferometry you can buy.

### HOLOGRAPHY SHEAROGRAPHY SPECKLE CORRELATION PROJECTED FRINGE MOIRÉ

With phase-step imaging for a real-time display of either fringes or their fringe locus function (i.e. phase), robust phase unwrapping, integrated frequency generators, available as separate heads on a light composite breadboard with up to 200mw of green laser light integrally mounted for simple point-and-shoot operation, or as a single unit with interchangeable modules.

Available from **Karl Stetson Associates**,  
2060 South Street, Coventry, CT 06238  
Phone/fax 860/742-8414  
Email 74267.2560@CompuServe.com.

# Extensometers

Strain Measurement For




Epsilon

## Work With Nearly All Brands Of Testers

21 Models Cover All Common Tests

- Travel ranges from 1% to 2000% strain
- Gage lengths from 0.25 to 10 inches (6 to 250 mm)
- Temperature ranges from -265 to 1600 °C
- Also Laser Extensometer



 **Epsilon**  
TECHNOLOGY CORP

**307-733-8360**  
fax 307-733-8375

3975 S. Highway 89, Jackson, WY 83001 USA